


ANALISIS GRANULOMETRICOS

MUESTRA: IP85

UTM X: 647804


UTM Y: 3209002



TAMICES ASTM		Peso retenido (gramos)	% Retenido	% Que pasa
n°4	4.75 mm	0.37 (100 %C)	0.4%	99.6%
n°10	2 mm	0.00 (0 %C)	0.4%	99.6%
n°18	1 mm	0.05 (100 %C)	0.4%	99.6%
n°25	0.71 mm	0.26 (100 %C)	0.7%	99.3%
n°35	0.5 mm	2.99 (0 %C)	3.7%	96.3%
n°60	0.25 mm	62.84 (0 %C)	66.5%	33.5%
n°80	0.18 mm	24.48 (0 %C)	91.0%	9.0%
n°120	0.125 mm	8.75 (0 %C)	99.7%	0.3%
n°230	0.063 mm	0.21 (0 %C)	99.9%	0.1%
Finos	<0,063 mm	0.05 (0 %C)	100.0%	0.0%

% FINOS	0.05%
% CASCAJO	0.68%
D16	0.449
D50	0.314
D84	0.200
Media	0.321
σ	0.124
M. distribuc.	0.324

MODA ARENAS MEDIAS



	D50	
Cantos y gravas	>2	mm
Arena muy gruesa	1-2	mm
Arena gruesa	0,5-1	mm
Arena media	0,25-0,5	mm
Arena fina	0,125-0,25	mm
Arena muy fina	0,062-0,125	mm
Fango	<0,062	mm