


## ANALISIS GRANULOMETRICOS

MUESTRA: IP135

UTM X: 649435


UTM Y: 3223270



TAMICES ASTM		Peso retenido (gramos)	% Retenido	% Que pasa
n°4	4.75 mm	0.00 ( 0 %C)	0.0%	100.0%
n°10	2 mm	0.00 ( 0 %C)	0.0%	100.0%
n°18	1 mm	0.00 ( 0 %C)	0.0%	100.0%
n°25	0.71 mm	0.07 ( 0 %C)	0.1%	99.9%
n°35	0.5 mm	0.22 ( 0 %C)	0.3%	99.7%
n°60	0.25 mm	28.39 ( 0 %C)	28.7%	71.3%
n°80	0.18 mm	43.16 ( 0 %C)	71.8%	28.2%
n°120	0.125 mm	26.73 ( 0 %C)	98.6%	1.4%
n°230	0.063 mm	1.37 ( 0 %C)	99.9%	0.1%
Finos	<0,063 mm	0.07 ( 0 %C)	100.0%	0.0%

% FINOS	0.07%
% CASCAJO	0.00%
<b>D16</b>	0.362
<b>D50</b>	0.215
<b>D84</b>	0.155
<b>Media</b>	0.244
<b>σ</b>	0.103
<b>M. distribuc.</b>	0.258

### MODA ARENAS FINAS



	<u>D50</u>	
Cantos y gravas	>2	mm
Arena muy gruesa	1-2	mm
Arena gruesa	0,5-1	mm
Arena media	0,25-0,5	mm
Arena fina	0,125-0,25	mm
Arena muy fina	0,062-0,125	mm
Fango	<0,062	mm