


## ANALISIS GRANULOMETRICOS

MUESTRA: IP35

UTM X: 640201


UTM Y: 3221636



TAMICES ASTM		Peso retenido (gramos)	% Retenido	% Que pasa
n°4	4.75 mm	0.00 ( 0 %C)	0.0%	100.0%
n°10	2 mm	0.00 ( 0 %C)	0.0%	100.0%
n°18	1 mm	0.00 ( 0 %C)	0.0%	100.0%
n°25	0.71 mm	0.10 ( 50 %C)	0.1%	99.9%
n°35	0.5 mm	1.43 ( 0 %C)	1.5%	98.5%
n°60	0.25 mm	40.08 ( 0 %C)	41.6%	58.4%
n°80	0.18 mm	30.06 ( 0 %C)	71.7%	28.3%
n°120	0.125 mm	24.24 ( 0 %C)	95.9%	4.1%
n°230	0.063 mm	4.01 ( 0 %C)	99.9%	0.1%
Finos	<0,063 mm	0.10 ( 0 %C)	100.0%	0.0%

% FINOS	0.10%
% CASCAJO	0.05%
<b>D16</b>	0.409
<b>D50</b>	0.230
<b>D84</b>	0.152
<b>Media</b>	0.264
<b>σ</b>	0.129
<b>M. distribuc.</b>	0.281

### MODA ARENAS FINAS



	<u>D50</u>	
Cantos y gravas	>2	mm
Arena muy gruesa	1-2	mm
Arena gruesa	0,5-1	mm
Arena media	0,25-0,5	mm
Arena fina	0,125-0,25	mm
Arena muy fina	0,062-0,125	mm
Fango	<0,062	mm