


ANALISIS GRANULOMETRICOS

MUESTRA: IP30

UTM X: 640740


UTM Y: 3221760



TAMICES ASTM		Peso retenido (gramos)	% Retenido	% Que pasa
n°4	4.75 mm	0.00 (0 %C)	0.0%	100.0%
n°10	2 mm	0.06 (0 %C)	0.1%	99.9%
n°18	1 mm	0.06 (0 %C)	0.1%	99.9%
n°25	0.71 mm	0.11 (10 %C)	0.2%	99.8%
n°35	0.5 mm	0.34 (0 %C)	0.6%	99.4%
n°60	0.25 mm	32.54 (0 %C)	33.1%	66.9%
n°80	0.18 mm	39.02 (0 %C)	72.1%	27.9%
n°120	0.125 mm	24.80 (0 %C)	96.9%	3.1%
n°230	0.063 mm	2.96 (0 %C)	99.9%	0.1%
Finos	<0,063 mm	0.11 (0 %C)	100.0%	0.0%

% FINOS	0.11%
% CASCAJO	0.01%
D16	0.381
D50	0.220
D84	0.154
Media	0.252
σ	0.114
M. distribuc.	0.268

MODA ARENAS FINAS



	<u>D50</u>	
Cantos y gravas	>2	mm
Arena muy gruesa	1-2	mm
Arena gruesa	0,5-1	mm
Arena media	0,25-0,5	mm
Arena fina	0,125-0,25	mm
Arena muy fina	0,062-0,125	mm
Fango	<0,062	mm