


## ANALISIS GRANULOMETRICOS

MUESTRA: D759

UTM X: 652237


UTM Y: 3223979



TAMICES ASTM		Peso retenido (gramos)	% Retenido	% Que pasa
n°4	4.75 mm	0.00 ( 0 %C)	0.0%	100.0%
n°10	2 mm	3.03 ( 100 %C)	3.0%	97.0%
n°18	1 mm	14.00 ( 100 %C)	17.0%	83.0%
n°25	0.71 mm	10.97 ( 100 %C)	28.0%	72.0%
n°35	0.5 mm	10.27 ( 0 %C)	38.3%	61.7%
n°60	0.25 mm	18.79 ( 0 %C)	57.1%	42.9%
n°80	0.18 mm	12.14 ( 0 %C)	69.2%	30.8%
n°120	0.125 mm	24.15 ( 0 %C)	93.3%	6.7%
n°230	0.063 mm	5.83 ( 0 %C)	99.2%	0.8%
Finos	<0,063 mm	0.82 ( 0 %C)	100.0%	0.0%

% FINOS	1.13%
% CASCAJO	28.00%
<b>D16</b>	0.483
<b>D50</b>	0.210
<b>D84</b>	0.136
<b>Media</b>	0.276
<b>σ</b>	0.174
<b>M. distribuc.</b>	0.310

### MODA ARENAS FINAS



	<u>D50</u>	
Cantos y gravas	>2	mm
Arena muy gruesa	1-2	mm
Arena gruesa	0,5-1	mm
Arena media	0,25-0,5	mm
Arena fina	0,125-0,25	mm
Arena muy fina	0,062-0,125	mm
Fango	<0,062	mm