


## ANALISIS GRANULOMETRICOS

MUESTRA: IP051


UTM X: 649344

UTM Y: 3233887



TAMICES ASTM		Peso retenido (gramos)	% Retenido	% Que pasa
n°4	4.75 mm	0.00 ( 0 %C)	0.0%	100.0%
n°10	2 mm	0.00 ( 0 %C)	0.0%	100.0%
n°18	1 mm	0.00 ( 0 %C)	0.0%	100.0%
n°25	0.71 mm	0.00 ( 0 %C)	0.0%	100.0%
n°35	0.5 mm	0.08 ( 0 %C)	0.1%	99.9%
n°60	0.25 mm	4.18 ( 0 %C)	4.3%	95.7%
n°80	0.18 mm	49.21 ( 0 %C)	53.5%	46.5%
n°120	0.125 mm	44.86 ( 0 %C)	98.3%	1.7%
n°230	0.063 mm	1.59 ( 0 %C)	99.9%	0.1%
Finos	<0,063 mm	0.08 ( 0 %C)	100.0%	0.0%

% FINOS	0.08%
% CASCAJO	0.00%
<b>D16</b>	0.233
<b>D50</b>	0.185
<b>D84</b>	0.143
<b>Media</b>	0.187
<b>σ</b>	0.045
<b>M. distribuc.</b>	0.188



### MODA ARENAS FINAS

	D50	
Cantos y gravas	>2	mm
Arena muy gruesa	1-2	mm
Arena gruesa	0,5-1	mm
Arena media	0,25-0,5	mm
Arena fina	0,125-0,25	mm
Arena muy fina	0,062-0,125	mm
Fango	<0,062	mm