


## ANALISIS GRANULOMETRICOS

MUESTRA: IP24

UTM X: 641543


UTM Y: 3222134



TAMICES ASTM		Peso retenido (gramos)	% Retenido	% Que pasa
n°4	4.75 mm	0.00 ( 0 %C)	0.0%	100.0%
n°10	2 mm	0.00 ( 0 %C)	0.0%	100.0%
n°18	1 mm	0.00 ( 0 %C)	0.0%	100.0%
n°25	0.71 mm	0.00 ( 0 %C)	0.0%	100.0%
n°35	0.5 mm	0.00 ( 0 %C)	0.0%	100.0%
n°60	0.25 mm	8.51 ( 0 %C)	8.5%	91.5%
n°80	0.18 mm	31.71 ( 0 %C)	40.2%	59.8%
n°120	0.125 mm	50.62 ( 0 %C)	90.8%	9.2%
n°230	0.063 mm	9.08 ( 0 %C)	99.9%	0.1%
Finos	<0,063 mm	0.08 ( 0 %C)	100.0%	0.0%

% FINOS	0.08%
% CASCAJO	0.00%
<b>D16</b>	0.233
<b>D50</b>	0.169
<b>D84</b>	0.132
<b>Media</b>	0.178
<b>σ</b>	0.051
<b>M. distribuc.</b>	0.183

### MODA ARENAS FINAS



	<i>D50</i>	
<i>Cantos y gravas</i>	>2	mm
<i>Arena muy gruesa</i>	1-2	mm
<i>Arena gruesa</i>	0,5-1	mm
<i>Arena media</i>	0,25-0,5	mm
<i>Arena fina</i>	0,125-0,25	mm
<i>Arena muy fina</i>	0,062-0,125	mm
<i>Fango</i>	<0,062	mm