


## ANALISIS GRANULOMETRICOS

MUESTRA: IP43


UTM X: 630914

UTM Y: 3221588



TAMICES ASTM		Peso retenido (gramos)	% Retenido	% Que pasa
n°4	4.75 mm	6.65 ( 0 %C)	6.7%	93.3%
n°10	2 mm	4.61 ( 0 %C)	11.3%	88.7%
n°18	1 mm	3.75 ( 0 %C)	15.0%	85.0%
n°25	0.71 mm	1.71 ( 10 %C)	16.7%	83.3%
n°35	0.5 mm	5.14 ( 0 %C)	21.9%	78.1%
n°60	0.25 mm	37.22 ( 0 %C)	59.1%	40.9%
n°80	0.18 mm	17.52 ( 0 %C)	76.6%	23.4%
n°120	0.125 mm	14.23 ( 0 %C)	90.8%	9.2%
n°230	0.063 mm	6.32 ( 0 %C)	97.2%	2.8%
Finos	<0,063 mm	2.83 ( 0 %C)	100.0%	0.0%

<b>% FINOS</b>	2.84%
<b>% CASCAJO</b>	0.17%
<b>D16</b>	0.821
<b>D50</b>	0.310
<b>D84</b>	0.151
<b>Media</b>	0.428
<b>σ</b>	0.335
<b>M. distribuc.</b>	0.486



### MODA ARENAS MEDIAS

	<i>D50</i>	
<i>Cantos y gravas</i>	>2	mm
<i>Arena muy gruesa</i>	1-2	mm
<i>Arena gruesa</i>	0,5-1	mm
<i>Arena media</i>	0,25-0,5	mm
<i>Arena fina</i>	0,125-0,25	mm
<i>Arena muy fina</i>	0,062-0,125	mm
<i>Fango</i>	<0,062	mm