


ANALISIS GRANULOMETRICOS

MUESTRA: IP55

UTM X: 651339


UTM Y: 3232968



| TAMICES ASTM | | Peso retenido (gramos) | % Retenido | % Que pasa |
|--------------|-----------|---------------------------|------------|------------|
| n°4 | 4.75 mm | 0.00 (0 %C) | 0.0% | 100.0% |
| n°10 | 2 mm | 1.13 (100 %C) | 1.1% | 98.9% |
| n°18 | 1 mm | 12.88 (100 %C) | 14.0% | 86.0% |
| n°25 | 0.71 mm | 24.81 (100 %C) | 38.8% | 61.2% |
| n°35 | 0.5 mm | 21.90 (0 %C) | 60.7% | 39.3% |
| n°60 | 0.25 mm | 26.79 (0 %C) | 87.5% | 12.5% |
| n°80 | 0.18 mm | 4.51 (0 %C) | 92.0% | 8.0% |
| n°120 | 0.125 mm | 4.04 (0 %C) | 96.1% | 3.9% |
| n°230 | 0.063 mm | 3.10 (0 %C) | 99.2% | 0.8% |
| Finos | <0,063 mm | 0.85 (0 %C) | 100.0% | 0.0% |

| | |
|----------------------|--------|
| % FINOS | 1.38% |
| % CASCAJO | 38.82% |
| D16 | 0.616 |
| D50 | 0.419 |
| D84 | 0.208 |
| Media | 0.414 |
| σ | 0.204 |
| M. distribuc. | 0.412 |

MODA ARENAS MEDIAS



| | <i>D50</i> | |
|-------------------------|-------------|----|
| <i>Cantos y gravas</i> | >2 | mm |
| <i>Arena muy gruesa</i> | 1-2 | mm |
| <i>Arena gruesa</i> | 0,5-1 | mm |
| <i>Arena media</i> | 0,25-0,5 | mm |
| <i>Arena fina</i> | 0,125-0,25 | mm |
| <i>Arena muy fina</i> | 0,062-0,125 | mm |
| <i>Fango</i> | <0,062 | mm |