


## ANALISIS GRANULOMETRICOS

MUESTRA: IP130

UTM X: 630031


UTM Y: 3199777



TAMICES ASTM		Peso retenido (gramos)	% Retenido	% Que pasa
n°4	4.75 mm	0.00 ( 0 %C)	0.0%	100.0%
n°10	2 mm	0.00 ( 0 %C)	0.0%	100.0%
n°18	1 mm	0.04 ( 50 %C)	0.0%	100.0%
n°25	0.71 mm	0.08 ( 50 %C)	0.1%	99.9%
n°35	0.5 mm	0.58 ( 50 %C)	0.7%	99.3%
n°60	0.25 mm	26.58 ( 0 %C)	27.3%	72.7%
n°80	0.18 mm	39.77 ( 0 %C)	67.0%	33.0%
n°120	0.125 mm	31.46 ( 0 %C)	98.5%	1.5%
n°230	0.063 mm	1.46 ( 0 %C)	100.0%	0.0%
Finos	<0,063 mm	0.04 ( 0 %C)	100.0%	0.0%

<b>% FINOS</b>	0.04%
<b>% CASCAJO</b>	0.35%
<b>D16</b>	0.353
<b>D50</b>	0.210
<b>D84</b>	0.150
<b>Media</b>	0.238
<b>σ</b>	0.102
<b>M. distribuc.</b>	0.252

### MODA ARENAS FINAS



	<u>D50</u>	
<i>Cantos y gravas</i>	>2	mm
<i>Arena muy gruesa</i>	1-2	mm
<i>Arena gruesa</i>	0,5-1	mm
<i>Arena media</i>	0,25-0,5	mm
<i>Arena fina</i>	0,125-0,25	mm
<i>Arena muy fina</i>	0,062-0,125	mm
<i>Fango</i>	<0,062	mm