


## ANALISIS GRANULOMETRICOS

MUESTRA: IP45

UTM X: 630745


UTM Y: 3221441



TAMICES ASTM		Peso retenido (gramos)	% Retenido	% Que pasa
n°4	4.75 mm	0.00 ( 0 %C)	0.0%	100.0%
n°10	2 mm	0.09 ( 50 %C)	0.1%	99.9%
n°18	1 mm	0.55 ( 50 %C)	0.6%	99.4%
n°25	0.71 mm	0.83 ( 50 %C)	1.5%	98.5%
n°35	0.5 mm	5.36 ( 0 %C)	6.8%	93.2%
n°60	0.25 mm	54.66 ( 0 %C)	61.5%	38.5%
n°80	0.18 mm	21.05 ( 0 %C)	82.5%	17.5%
n°120	0.125 mm	14.68 ( 0 %C)	97.2%	2.8%
n°230	0.063 mm	2.68 ( 0 %C)	99.9%	0.1%
Finos	<0,063 mm	0.09 ( 0 %C)	100.0%	0.0%

% FINOS	0.09%
% CASCAJO	0.74%
<b>D16</b>	0.455
<b>D50</b>	0.301
<b>D84</b>	0.174
<b>Media</b>	0.310
<b>σ</b>	0.141
<b>M. distribuc.</b>	0.315

## MODA ARENAS MEDIAS



	<i>D50</i>	
<i>Cantos y gravas</i>	>2	mm
<i>Arena muy gruesa</i>	1-2	mm
<i>Arena gruesa</i>	0,5-1	mm
<i>Arena media</i>	0,25-0,5	mm
<i>Arena fina</i>	0,125-0,25	mm
<i>Arena muy fina</i>	0,062-0,125	mm
<i>Fango</i>	<0,062	mm