


## ANALISIS GRANULOMETRICOS

MUESTRA: IP33

UTM X: 640344


UTM Y: 3221652



TAMICES ASTM		Peso retenido (gramos)	% Retenido	% Que pasa
n°4	4.75 mm	0.00 ( 0 %C)	0.0%	100.0%
n°10	2 mm	0.00 ( 0 %C)	0.0%	100.0%
n°18	1 mm	0.00 ( 0 %C)	0.0%	100.0%
n°25	0.71 mm	0.07 ( 10 %C)	0.1%	99.9%
n°35	0.5 mm	0.34 ( 0 %C)	0.4%	99.6%
n°60	0.25 mm	37.96 ( 0 %C)	38.4%	61.6%
n°80	0.18 mm	36.39 ( 0 %C)	74.8%	25.2%
n°120	0.125 mm	23.05 ( 0 %C)	97.8%	2.2%
n°230	0.063 mm	2.05 ( 0 %C)	99.9%	0.1%
Finos	<0,063 mm	0.14 ( 0 %C)	100.0%	0.0%

% FINOS	0.14%
% CASCAJO	0.01%
<b>D16</b>	0.397
<b>D50</b>	0.228
<b>D84</b>	0.158
<b>Media</b>	0.261
<b>σ</b>	0.120
<b>M. distribuc.</b>	0.278

### MODA ARENAS FINAS



	<u>D50</u>	
Cantos y gravas	>2	mm
Arena muy gruesa	1-2	mm
Arena gruesa	0,5-1	mm
Arena media	0,25-0,5	mm
Arena fina	0,125-0,25	mm
Arena muy fina	0,062-0,125	mm
Fango	<0,062	mm