


## ANALISIS GRANULOMETRICOS

MUESTRA: IP76


UTM X: 618210

UTM Y: 3191173



TAMICES ASTM		Peso retenido (gramos)	% Retenido	% Que pasa
n°4	4.75 mm	1.80 ( 100 %C)	1.8%	98.2%
n°10	2 mm	0.00 ( 0 %C)	1.8%	98.2%
n°18	1 mm	0.06 ( 100 %C)	1.9%	98.1%
n°25	0.71 mm	0.06 ( 100 %C)	1.9%	98.1%
n°35	0.5 mm	0.06 ( 0 %C)	2.0%	98.0%
n°60	0.25 mm	29.99 ( 0 %C)	32.0%	68.0%
n°80	0.18 mm	42.95 ( 0 %C)	74.9%	25.1%
n°120	0.125 mm	23.52 ( 0 %C)	98.4%	1.6%
n°230	0.063 mm	1.50 ( 0 %C)	99.9%	0.1%
Finos	<0,063 mm	0.06 ( 0 %C)	100.0%	0.0%

% FINOS	0.06%
% CASCAJO	1.92%
<b>D16</b>	0.370
<b>D50</b>	0.219
<b>D84</b>	0.158
<b>Media</b>	0.249
<b>σ</b>	0.106
<b>M. distribuc.</b>	0.264



## MODA ARENAS FINAS

	D50	
Cantos y gravas	>2	mm
Arena muy gruesa	1-2	mm
Arena gruesa	0,5-1	mm
Arena media	0,25-0,5	mm
Arena fina	0,125-0,25	mm
Arena muy fina	0,062-0,125	mm
Fango	<0,062	mm