


# ANALISIS GRANULOMETRICOS

MUESTRA: IP80

UTM X: 618877


UTM Y: 3191325



TAMICES ASTM		Peso retenido (gramos)	% Retenido	% Que pasa
n°4	4.75 mm	0.00 ( 0 %C)	0.0%	100.0%
n°10	2 mm	0.00 ( 0 %C)	0.0%	100.0%
n°18	1 mm	0.07 ( 100 %C)	0.1%	99.9%
n°25	0.71 mm	0.21 ( 100 %C)	0.3%	99.7%
n°35	0.5 mm	0.69 ( 0 %C)	1.0%	99.0%
n°60	0.25 mm	47.12 ( 0 %C)	48.1%	51.9%
n°80	0.18 mm	39.14 ( 0 %C)	87.2%	12.8%
n°120	0.125 mm	12.49 ( 0 %C)	99.7%	0.3%
n°230	0.063 mm	0.28 ( 0 %C)	100.0%	0.0%
Finos	<0,063 mm	0.00 ( 0 %C)	100.0%	0.0%

% FINOS	0.00%
% CASCAJO	0.28%
D16	0.419
D50	0.246
D84	0.186
Media	0.284
σ	0.117
M. distribuc.	0.302

## MODA ARENAS FINAS



	D50	
Cantos y gravas	>2	mm
Arena muy gruesa	1-2	mm
Arena gruesa	0,5-1	mm
Arena media	0,25-0,5	mm
Arena fina	0,125-0,25	mm
Arena muy fina	0,062-0,125	mm
Fango	<0,062	mm