


## ANALISIS GRANULOMETRICOS

MUESTRA: IP44

UTM X: 630840


UTM Y: 3221523



TAMICES ASTM		Peso retenido (gramos)	% Retenido	% Que pasa
n°4	4.75 mm	0.00 ( 0 %C)	0.0%	100.0%
n°10	2 mm	0.00 ( 0 %C)	0.0%	100.0%
n°18	1 mm	0.17 ( 90 %C)	0.2%	99.8%
n°25	0.71 mm	0.17 ( 90 %C)	0.3%	99.7%
n°35	0.5 mm	2.05 ( 0 %C)	2.4%	97.6%
n°60	0.25 mm	69.17 ( 0 %C)	71.6%	28.4%
n°80	0.18 mm	20.58 ( 0 %C)	92.1%	7.9%
n°120	0.125 mm	6.92 ( 0 %C)	99.1%	0.9%
n°230	0.063 mm	0.85 ( 0 %C)	99.9%	0.1%
Finos	<0,063 mm	0.09 ( 0 %C)	100.0%	0.0%

% FINOS	0.09%
% CASCAJO	0.31%
<b>D16</b>	0.450
<b>D50</b>	0.327
<b>D84</b>	0.208
<b>Media</b>	0.328
<b>σ</b>	0.121
<b>M. distribuc.</b>	0.329

## MODA ARENAS MEDIAS



	<u>D50</u>	
Cantos y gravas	>2	mm
Arena muy gruesa	1-2	mm
Arena gruesa	0,5-1	mm
Arena media	0,25-0,5	mm
Arena fina	0,125-0,25	mm
Arena muy fina	0,062-0,125	mm
Fango	<0,062	mm