


## ANALISIS GRANULOMETRICOS

MUESTRA: IP47


UTM X: 630755

UTM Y: 3221190



TAMICES ASTM		Peso retenido (gramos)	% Retenido	% Que pasa
n°4	4.75 mm	2.24 ( 0 %C)	2.2%	97.8%
n°10	2 mm	3.25 ( 10 %C)	5.5%	94.5%
n°18	1 mm	1.74 ( 10 %C)	7.2%	92.8%
n°25	0.71 mm	0.87 ( 50 %C)	8.1%	91.9%
n°35	0.5 mm	4.05 ( 0 %C)	12.1%	87.9%
n°60	0.25 mm	47.72 ( 0 %C)	59.9%	40.1%
n°80	0.18 mm	18.08 ( 0 %C)	77.9%	22.1%
n°120	0.125 mm	9.83 ( 0 %C)	87.8%	12.2%
n°230	0.063 mm	7.38 ( 0 %C)	95.2%	4.8%
Finos	<0,063 mm	4.84 ( 0 %C)	100.0%	0.0%

% FINOS	4.89%
% CASCAJO	0.93%
<b>D16</b>	0.476
<b>D50</b>	0.299
<b>D84</b>	0.145
<b>Media</b>	0.307
<b>σ</b>	0.165
<b>M. distribuc.</b>	0.311



### MODA ARENAS MEDIAS

	<u>D50</u>	
Cantos y gravas	>2	mm
Arena muy gruesa	1-2	mm
Arena gruesa	0,5-1	mm
Arena media	0,25-0,5	mm
Arena fina	0,125-0,25	mm
Arena muy fina	0,062-0,125	mm
Fango	<0,062	mm