


ANALISIS GRANULOMETRICOS

MUESTRA: IP68

UTM X: 646486


UTM Y: 3208073



TAMICES ASTM		Peso retenido (gramos)	% Retenido	% Que pasa
n°4	4.75 mm	0.00 (0 %C)	0.0%	100.0%
n°10	2 mm	0.00 (0 %C)	0.0%	100.0%
n°18	1 mm	0.00 (0 %C)	0.0%	100.0%
n°25	0.71 mm	1.99 (10 %C)	2.0%	98.0%
n°35	0.5 mm	32.02 (0 %C)	34.0%	66.0%
n°60	0.25 mm	63.40 (0 %C)	97.4%	2.6%
n°80	0.18 mm	2.35 (0 %C)	99.8%	0.2%
n°120	0.125 mm	0.18 (0 %C)	99.9%	0.1%
n°230	0.063 mm	0.06 (0 %C)	100.0%	0.0%
Finos	<0,063 mm	0.00 (0 %C)	100.0%	0.0%

% FINOS	0.00%
% CASCAJO	0.20%
D16	0.617
D50	0.437
D84	0.303
Media	0.452
σ	0.157
M. distribuc.	0.460

MODA ARENAS MEDIAS



	<u>D50</u>	
Cantos y gravas	>2	mm
Arena muy gruesa	1-2	mm
Arena gruesa	0,5-1	mm
Arena media	0,25-0,5	mm
Arena fina	0,125-0,25	mm
Arena muy fina	0,062-0,125	mm
Fango	<0,062	mm